

Complete Unit With 20A Duplex,  
(2) 1/2" Diameter Holes for Low  
Voltage Wiring, Gray

By Hubbell Wiring Device-Kellems  
Catalog # [PT7FSDGYA](#)

In-Floor Delivery Systems, Fire-Rated Poke-Throughs, Flush  
Duplex Series, Complete Unit With 20A Duplex, (2) 1/2"  
Diameter Holes for Low Voltage Wiring, Gray

General

Application - For Use On	Carpet
Catalog Number	PT7FSDGYA
EU RoHS Indicator	No
Finish Type	Gray
Item Type	3" Fire-Rated Poke Through Component
Knockouts	Duplex Flip Covers and (2) 1/2" Diameter Holes for Low Voltage Wiring
Material - Mounting Hardware	Step-Down Installation
Number Of Outlets	(1) 20A Duplex Receptacle and (2) 1/2" Diameter Holes for Low Voltage Wiring
Specifications	<ul style="list-style-type: none"><li>Cover Material - Thermoplastic cover with aluminum flange</li><li>Floor thickness - 2 1/4 to 7 in. (57.2 to 177.8)</li><li>Mounting - 3 in. (76.2) cored concrete diameter through hole</li></ul>



Style	FRPT - Complete Kits
UPC	783585494074

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none"><li>cULus Listed</li><li>Meets ADA Standards</li><li>UL 514A Listed</li></ul>
----------------------	---

Logistics

Carton Quantity	1
-----------------	---

Product Assets

- [Catalog Page - WDK P-32 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - PT7FSDGYA AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD1962\\_INSTALLINST](#)
- [Literature - Delivery Systems Product Guide](#)
- [Sales Drawings - WDK\\_PT7FSDGY\\_DRAWING\\_PDF](#)
- [Specifications - PT7FSDGYA Specification Sheet English](#)
- [Specifications - PT7FSDGYA Specification Sheet French](#)
- [Specifications - PT7FSDGYA](#)
- [Warranty - Industrial & Commercial Products](#)