

Switches and Lighting Controls,
Combination Devices, Residential
Grade, 2) Single Pole Toggles, 15A
120V AC, Self Grounding, Side
Wired, Light Almond

By Hubbell Wiring Device-Kellems
Catalog # [RC101LA](#)



Two Single-Pole Toggle Combination Device, Residential, 15A
120V AC, Self Grounding, Side Wired

Performance

Environmental - Operating temperature - -20°C to 60°C

General

Action	Snap Switch
Actuator	Toggle
Catalog Number	RC101LA
Contact Configuration	Two Position
EU RoHS Indicator	Yes
Item Type	Traditional Switch Combo Devices
Material - Mounting Hardware	Mounting Screws
Number Of Poles	2) Single Pole
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact
UPC	883778119064

Dimensions

Display Size	Standard Size
--------------	---------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Side Wired
Contact Rating	15A
Current / Amperage Rating	15 A

Current Rating	15 A
Voltage Rating	120 VAC
Voltage Rating Description	120 VAC
Wattage	1800

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
Pallet Quantity	7200

Product Assets

- [Catalog Page - WDK Z-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RC101LA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2132_INSTALLINST](#)
- [Literature - Residential Catalog](#)
- [Literature - Residential Product Guide](#)
- [Sales Drawings - WDK_RC101_DRAWINGS_PDF](#)
- [Specifications - RC101LA Specification Sheet](#)
- [Specifications - WIRING_RC101LA_spec](#)
- [Specifications - RC101LA Specification Sheet French](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)
- [Video - Tradeselect Devices](#)
- [Video - Tradeselect Devices](#)