

Combination Devices, Residential Grade,
Decorator Series, 1) Single Pole Rocker, 1)
Tamper Resistant Single Receptacle, 15A
120V AC, Side Wired

By Hubbell Wiring Device-Kellems
Catalog # [RCD108BKTR](#)

Switches and Lighting Controls, Combination Devices, Residential
Grade, Decorator Series, 1) Single Pole Rocker, 1) Tamper Resistant
Single Receptacle, 15A 120V AC, Side Wired

Features

- Smooth, quiet rocker
- Low profile, less than 1 inch deep
- Self-grounding feature is standard

Application

Residential

Performance

Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute, Electrical - Endurance - 30,000 cycles minimum, Electrical - Max. working voltage - 120V, Electrical - Overload - 1.5 times rating, Environmental - Flammability - UL V0, Environmental - Operating temperatures - Maximum continuous 60°C, minimum -20°C (without impact), Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only, push wire: #14 AWG solid copper wire only

Specifications

Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Industry Standard(s)	• CSA Certified • UL Listed E3896

Conductor

Number Of Poles	1) Single Pole
-----------------	----------------

Configuration

Contact Configuration	Two Position
-----------------------	--------------

Current

Amperage Rating	15 A
Voltage Rating Description	125 VAC
Current Rating	15 A
Voltage Rating	125 VAC



Wattage	1875 W
Connectivity	Side Wired
Current / Amperage Rating	15 A
Contact Rating	15A

Dimensions

Display Size	Standard Size
Weight	0.15 lb.

General

Specifications	• Base and body - PVC • Mounting strap - Galvanized steel • Rocker - Polycarbonate • Terminal screws - Steel • Terminals - Brass
UPC	883778302343
Material - Mounting Hardware	Mounting Screws
Item Type	Decorator Switch and Receptacle Combo Devices

Logistics

Carton Quantity	10
-----------------	----

Operational

Actuator	Rocker
Action	Snap Switch
Operating Cycles	30,000 Minimum
Operating Temperature	Max Continuous- 60 Degrees C, Minimum- -20 Without Impact

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)