

20A Kitchen Counter Receptacle,
Surface Mount, Brass

By Hubbell Wiring Device-Kellems
Catalog # [RCT220BR](#)

20A Kitchen Counter Receptacle, Surface Mount, Brass



Features

- Spill water tested
- UL Listed for countertop installation.
- Permanent installation ready (suitable for MC cable or non-metallic sheath cable)
- Push down to pop-up function is rated for a minimum of 10,000 cycles
- Easy installations - simply drop in and tighten.

Application

Power on Counter Top

General

Catalog Number	RCT220BR
Color	Brass
Construction	Fabricated
Construction Material - Main	220 Meunt
EU RoHS Indicator	Contact Manufacturer
Material	220 Meunt
Mounting Type	In Kitchen Counter Top
Number Of Outlets	1 Duplex
Number Of Poles	2
Series	Countertop Receptacle
Size	Standard Sized
Style	Surface
Sub Brand	Furniture Boxes
Type	Power Only
UPC	883778309496

Dimensions

Dimensions	4.20 in x 4.20 in x 6.48 in
Height	6.48 in
Length	4.2 in
Width	4.2 in

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Conductor Related

Cable Entry	Kos in Bottom
Number Of Wires	3

Certifications And Compliance

Industry Standard(s)	UL
Nema Rating	5-20R

Logistics

Carton Quantity	10
Pallet Quantity	630

Product Assets

[360 Product View - BRYA_RCT220NI](#)
[3D Product View - BRYA_RCT220NI](#)
[Catalog Page - WDK Z-25 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RCT220BR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2741_INSTALLINST](#)
[Literature - Residential Catalog](#)
[Sales Drawings - WDK_RCT220_DRAWING_PDF](#)
[Specifications - Wiring RCT220BR Specification Sheet](#)
[Specifications - RCT220BR Specification Sheet](#)
[Specifications - RCT220BR Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Hubbell Tri-Power Pop-Up Receptacle](#)
[Video - Tamper-Resistant Receptacles](#)
[Video - Tamper-Resistant Receptacles](#)