



Switches and Lighting Controls, Dimmer, Rotary, Single Pole, 600W 120V AC, Ivory or White

By Hubbell Wiring Device-Kellems
Catalog # [RD600PDK](#)

Switches and Lighting Controls, Dimmer, Rotary, Single Pole,
600W 120V AC, Ivory or White.



Features

- No Neutral Required
- Low End Adjustment for Fine Tuning

General

Application - For Use On	Only use with Compatible Dimmable Bulbs
Color	<ul style="list-style-type: none">• Ivory and White• Ivoire et blanc
Construction	Metal Strap, Polycarbonate Front
Environmental Conditions	Indoor Use Only
Number Of Poles	Single Pole
Number of Gang(s)	1-Gang
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Orientation	Vertical
Style	Rotary Dimmer
Type	<ul style="list-style-type: none">• Incandescent• Incandescent
UPC	883778117060

Dimensions

Depth	1.3 in
Height	4.1 in
Width	2.2 in

Electrical Ratings

Amperage Rating	5 A
Voltage Rating	120 VAC
Voltage Rating Description	120V AC
Wattage	600 W

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	6
-----------------	---

Product Assets

[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - RD600PDK AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2291_INSTALLINST](#)
[Sales Drawings - WDK_RD600_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tradeselect Devices](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-RD600PDK-SPEC-EN | REV 1/2024