

J-Load Media Outlet, 15A 125V
Tamper Resistant Receptacle, Cat 6
Jack, F Coax, Decorator Frame,
Black

By Hubbell Wiring Device-Kellems
Catalog # [RJ650BKTR](#)



J-Load Media Outlet, 15A 125V Tamper Resistant Receptacle, Cat 6 Jack, F Coax, Decorator Frame, Black

Features

- Custom box mounting
- Accepts any snap fit jack configuration
- Isolates low voltage and power in the same box

General

Catalog Number	RJ650BKTR
Contact	Beryllium Copper, Brass
EU RoHS Indicator	Yes
Item Type	Complete Unit
Material - Mounting Hardware	Screw Mounting
Temperature Rating	Per TIA
UPC	883778302466

Dimensions

Display Size	1-Gang Standard Sized
--------------	-----------------------

Electrical Ratings

Connectivity	Terminal Screws for Receptacle
Contact Resistance	100 Ohm
Withstand Voltage	1000V RMS, 1414V DC

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Brochures - Floorbox Selection Guide](#)
[Catalog Page - WDK Z-21 Catalog Page](#)
[Catalog Page - WDK Z-22 Catalog Page](#)
[Catalog Page - WDK Z-27 Catalog Page](#)
[Catalog Page - WDK Z-18 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RJ650BKTR AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2198_INSTALLINST](#)
[Literature - Residential Product Guide](#)
[Sales Drawings - WDK_RJ650TR_DRAWING_PDF](#)
[Specifications - WIRING_RJ650BKTR_spec](#)
[Specifications - RJ650BKTR Specification Sheet French](#)
[Specifications - RJ650BKTR Specification Sheet](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tamper-Resistant Receptacles](#)
[Video - Tamper-Resistant Receptacles](#)
[Video - Tradeselect Devices](#)