

Lamp Holders and Sockets, Mogul Base, 4KV Pulse Start, 12" Leads, Screw Mounted

By Hubbell Wiring Device-Kellems
Catalog # [RL4221](#)

Lamp Holders and Sockets, Mogul Base, 4KV Pulse Start, 12" Leads, Screw Mounted

Features

- Mogul Base
- 4KV Pulse Start
- 12" Leads
- Screw Mounted

Application

HID Incandescent

Performance

- Electrical - Rating - 1500W, 600V Max, 5KV Pulse
- Mechanical - Terminal Accommodation - Wire leads: #14 AWG SF-2 (SEW-2) 200° C, 600V glass braid, 12 inch long, stripped 1/2 inch wire

General

Catalog Number	RL4221
Color	White
EU RoHS Indicator	No
Item Type	Replacement Incandescent Lampholders
Lamp Size	Mogul Base
Material	Composite
Material - Mounting Hardware	Screw Mounting
Series	Lampholders
Specifications	<ul style="list-style-type: none">• Lamp Type - E39 socket• Material - Glazed porcelain body with ceramic arc shield Screw shell: Brass with nickel plate



Type	<ul style="list-style-type: none">• Mounting - Screw mount, 12 inch leads HID Incandescent, Porcelain Keyless
UPC	883778304033

Electrical Ratings

Amperage Rating	2.5 A
Connectivity	12" Leads
Current / Amperage Rating	2.5 A
Current Rating	2.5 A
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK BB-8 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2362_INSTALLINST](#)
[Sales Drawings - WDK_RL4221_DRAWING_PDF](#)
[Specifications - RL4221](#)
[Specifications - RL4221 Specification Sheet English](#)
[Specifications - RL4221 Specification Sheet French](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

