

Fluorescent Lamp Holders,
Compact Type, 18-55 Watt 2G11, 90
Degree Horizontal Mount, Snap-In

By Hubbell Wiring Device-Kellems
Catalog # [RL42G11H9](#)

Fluorescent Lamp Holders, Compact Type, 18-55 Watt 2G11, 90
Degree Horizontal Mount, Snap-In

Features

- Compact Type
- 18-55 Watt 2G11
- 90 Degree Horizontal Mount
- Snap-In

Application

Compact Fluorescent

Performance

- Electrical - Rating - 26-32W lamp type, 75W, 600V
- Mechanical - Terminal Accommodation - Push-in wire terminals for #18 AWG solid or twist and tin stripped 7/16 inch wire

General

Catalog Number	RL42G11H9
EU RoHS Indicator	No
Item Type	Fluorescent Lampholders
Lamp Size	2-G11 Base 4) Pin
Material	Composite
Material - Mounting Hardware	Vertical Snap-In
Series	Lampholders
Specifications	• Lamp Type - 18-55W • Material - High Strength Polycarbonate



Type
UPC

- Mounting - Vertical 90°, snap-in
- Compact Fluorescent
883778303951

Electrical Ratings

Connectivity	Screw Terminals
Current Rating	Telephone/CATV
Frequency Rating	60 Hz
Voltage Rating	600V AC kV

Certifications And Compliance

Industry Standard(s)	• C/US UL Listed • CSA Certified
----------------------	--

Logistics

Carton Quantity	10
Pallet Quantity	2000

Product Assets

[Catalog Page - WDK BB-7 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2365_INSTALLINST](#)
[Sales Drawings - WDK_RL42G11H9_DRAWING_PDF](#)
[Specifications - RL42G11H9 Specification Sheet French](#)
[Specifications - WIRING_RL42G11H9_spec](#)
[Specifications - RL42G11H9 Specification Sheet](#)
[Warranty - tradeSELECT™ and netSELECT®](#)

