


RMS101ILAL

By Hubbell Wiring Device-Kellems  
Catalog # [RMS101ILAL](#)

Trade Select, Switches and Lighting Controls,Occupancy Sensor,  
Wall Mounted, 500 Watt, 125V, Illuminated, Almond.



Application

1-Button

General

Catalog Number	RMS101ILAL
Control Output	Input Voltage
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	PIR= Red LED
Item Type	Residential Wall Switches
Load Capacity	500W Incandescent @ 120V AC
Material - Mounting Hardware	Screw Mounting
Operating Cycles	6,000 Cycles Minimum
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)

Sensing Range	42 to 54 Inches above the Floor
UPC	883778301193

Electrical Ratings

Sensitivity	Adjustable W
Supply Voltage	120V AC V

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RMS101ILAL AutoCAD Drawing](#)
- [Installation Manuals - WIRING\\_PD2203\\_INSTALLINST](#)
- [Sales Drawings - WDK\\_RMS101\\_DRAWING\\_PDF](#)
- [Specifications - RMS101ILAL Specification Sheet French](#)
- [Specifications - RMS101ILAL Specification Sheet English](#)