

RMS120ILI

By Hubbell Wiring Device-Kellems
Catalog # [RMS120ILI](#)

Trade Select, Switches and Lighting Controls, Occupancy Sensor
With Night Light, Dimming, 500 Watts, 120V AC, 150 Degree
Field of View, Single Pole, Ivory

Application

No Buttons

General

Catalog Number	RMS120ILI
Control Output	Input Voltage
EU RoHS Indicator	No
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Indicator(s) Type	PIR= Red LED
Item Type	Residential Wall Switches
Load Capacity	500W Incandescent @ 120V AC
Material - Mounting Hardware	Screw Mounting
Operating Cycles	6,000 Cycles Minimum
Operating Temperature	32 Deg F to 104 Deg F (0 Deg C to 40 Deg C)
Sensing Range	42 to 54 Inches above the Floor
Specifications	<ul style="list-style-type: none">Product Type - Dimming Control Sensors



UPC

- Style - w/ Nightlight
883778301162

Electrical Ratings

Sensitivity	Adjustable W
Supply Voltage	120V AC V

Certifications And Compliance

Industry Standard(s)	<ul style="list-style-type: none">CEC Title 24 CertifiedcULus Listed
----------------------	---

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RMS120ILI AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2203_INSTALLINST](#)
- [Sales Drawings - WDK_RMS120_DRAWING_PDF](#)
- [Specifications - RMS120ILI Specification Sheet French](#)
- [Specifications - RMS120ILI Specification Sheet English](#)