

TradeSelect, Straight Blade Devices,
Residential Grade, Receptacles, Weather
and Tamper Resistant Duplex, 15A 125V, 5-
15R

By Hubbell Wiring Device-Kellems
Catalog # [RR15SLAWRTR](#)

TradeSelect, Straight Blade Devices, Residential Grade,
Receptacles, Weather and Tamper Resistant Duplex, 15A 125V, 2-
Pole 3-Wire Grounding, 5-15R, Self Grounding, Light Almond

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Application

Residential Receptacles

Performance

Environmental - Operating temperature - -20°C to 60°C,
Mechanical - Terminal - Terminal screws accepts up to #12 AWG,
Push wire designed for #14 AWG solid copper wire only

Specifications

Environmental Conditions	Weather Resistant
EU RoHS Indicator	No
Nema Rating	5-15R

Conductor

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG
Number Of Poles	2-Pole

Current

Amperage Rating	15 A
Voltage Rating Description	125 VAC
Current Rating	15 A



Voltage Rating	125 VAC
Wattage	1875
Connectivity	Push and Side Wire
Phase	Single Phase
Current / Amperage Rating	15 A

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

General

Color	Light Almond
Specifications	• Material - Thermoplastic • Number of Poles - 2 Pole • Product Type - Receptacle • Receptacle Type - Duplex
UPC	883778303043
Material - Mounting Hardware	Screw Mounting
Item Type	Traditional Duplex
Material	Thermoplastic

Logistics

Pallet Quantity	9000
Carton Quantity	10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[Spanish, French, English\]](#)