

TradeSelect, Straight Blade Devices,  
Residential Grade, Receptacles,  
Tamper Resistant Duplex, 15A 125V,  
2- Pole 3-Wire Grounding, 5-15R

By Hubbell Wiring Device-Kellems  
Catalog # [RR15SWTR](#)



TradeSelect, Straight Blade Devices, Residential Grade,  
Receptacles, Tamper Resistant Duplex, 15A 125V, 2- Pole 3-Wire  
Grounding, 5-15R, Self Grounding, White

Features

- Smooth indented face appearance
- Multiple-drive Slot/Phillips/Robertson head screws
- Tough thermoplastic ultrasonically welded cover and base

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

Catalog Number	RR15SWTR
Color	White
EU RoHS Indicator	Yes
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none"><li>• Material - Thermoplastic</li><li>• Number of Poles - 2 Pole</li><li>• Product Type - Receptacle</li><li>• Receptacle Type - Duplex</li></ul>
UPC	883778301544

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Push and Side Wire
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase

Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

- [Catalog Page - WDK Z-16 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RR15SWTR AutoCAD Drawing](#)
- [Literature - Residential Catalog](#)
- [Literature - Residential Product Guide](#)
- [Literature - Tamper-Resistant Receptacles](#)
- [Literature - Tamper-Resistant Receptacles for Residential Applications](#)
- [Sales Drawings - WDK\\_RR15STR\\_DRAWING\\_PDF](#)
- [Specifications - RR15SWTR Specification Sheet English](#)
- [Specifications - WIRING\\_RR15SWTR\\_spec](#)
- [Specifications - RR15SWTR Specification Sheet French](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)
- [Video - Tamper-Resistant Receptacles](#)
- [Video - Tamper-Resistant Receptacles](#)
- [Video - Tradeselect Devices](#)