

TradeSelect, Straight Blade Devices,
Receptacles, Residential Grade,
Duplex, 15A 125V, 2-Pole 3-Wire
Grounding, 5-15R, Push Terminals,
White

By Hubbell Wiring Device-Kellems
Catalog # [RR15W](#)



tradeSELECT® Straight Blade Receptacle, Residential Grade,
Duplex, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, Push
Terminals

Performance

- Environmental - Operating temperature - -20°C to 60°C
- Mechanical - Terminal - Terminal screws accepts up to #12 AWG, Push wire designed for #14 AWG solid copper wire only

General

Catalog Number	RR15W
EU RoHS Indicator	Yes
Item Type	Traditional Duplex
Material	Thermoplastic
Material - Mounting Hardware	Screw Mounting
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Material - Thermoplastic• Number of Poles - 2 Pole• Product Type - Receptacle• Receptacle Type - Duplex
UPC	883778100031

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	15 A
Connectivity	Push and Side Wire
Current / Amperage Rating	15 A
Current Rating	15 A
Phase	Single Phase

Voltage Rating	125 VAC
Voltage Rating Description	125 VAC
Wattage	1875

Conductor Related

Number Of Wires	3-Wire Grounding
Wire Size	#14 AWG to #12 AWG

Certifications And Compliance

Nema Rating	5-15R
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	11000

Product Assets

- [Catalog Page - WDK Z-16 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - RR15W AutoCAD Drawing](#)
- [Sales Drawings - WDK_RR15_DRAWINGS_PDF](#)
- [Specifications - Wiring_RR15W_spec](#)
- [Specifications - RR15W Specification Sheet French](#)
- [Specifications - RR15W Specification Sheet](#)
- [Warranty - tradeSELECT™ and netSELECT®](#)
- [Video - Tradeselect Devices](#)
- [Video - Tradeselect Devices](#)