

TradeSelect, Straight Blade, Single
Panel Mount Receptacle, 50A
125/250V, 3-Pole 4-Wire
Grounding, 14-50R, Black

By Hubbell Wiring Device-Kellems
Catalog # [RR450PM](#)

TradeSelect, Straight Blade, Single Panel Mount Receptacle, 50A
125/250V, 3-Pole 4-Wire Grounding, 14-50R, Black

Features

- Single Panel Mount Receptacle
- 50A 125/250V
- 3-Pole 4-Wire Grounding

Application

Residential Range and Dryer Devices

General

Catalog Number	RR450PM
EU RoHS Indicator	Yes
Environmental Conditions	Indoor Dry Unless Protected By Additional Means
Material - Mounting Hardware	Screw Mounting
Number Of Poles	3-Pole
Series	Heavy Duty
Type	Single Receptacle
UPC	883778100758

Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pressure Terminal Screws
Current / Amperage Rating	50 A
Current Rating	50 A
Phase	Single Phase



Voltage Rating	125/250 V
Voltage Rating Description	125/250 V
Wattage	12500

Conductor Related

Number Of Wires	4-Wire
Wire Size	#6 AWG

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	14-50R

Logistics

Carton Quantity	50
Pallet Quantity	4400

Product Assets

[Catalog Page - WDK Z-17 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RR450PM AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2193_INSTALLINST](#)
[Sales Drawings - WDK_RR450PM_DRAWING_PDF](#)
[Specifications - RR450PM Specification Sheet French](#)
[Specifications - RR450PM Specification Sheet](#)
[Specifications - WIRING_RR450PM_spec](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tradeselect Devices](#)
[Video - Tradeselect Devices](#)