



TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Brown

By Hubbell Wiring Device-Kellems
Catalog # [RSD215](#)

TradeSelect, Switches and Lighting Control, Rocker, Double Pole, 15A 120/277V AC, Brown.



Features

- Smooth, quiet rocker
- Self-grounding feature is standard
- Ultrasonically welded cover and base

General

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

UPC

883778101366

Certifications and Compliance

- | | |
|----------------------|-------------------|
| Industry Standard(s) | • CSA Certified |
| | • UL Listed E3896 |

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK Z-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Installation Manuals - WIRING_PD2444_INSTALLINST](#)
[Sales Drawings - WDK_RSD215_DRAWING_PDF](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tradeselect Devices](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-RSD215-SPEC-EN | REV 1/2024