

TradeSelect, Decorator Switch,
Residential Grade, Rocker Switch,
General Purpose AC, Three Way,
15A 120/277V AC, Push Back and
Side Wired

By Hubbell Wiring Device-Kellems
Catalog # [RSD315GY](#)



tradeSELECT® Decorator Switch, Residential Grade, Rocker
Switch, General Purpose AC, Three Way, 15A 120/277V AC, Push
Back and Side Wired

Performance

- Electrical - Dielectric voltage - Withstands 1,500V AC minimum for 1 minute
- Electrical - Endurance - 30,000 cycles minimum
- Electrical - Max. working voltage - 120V
- Electrical - Overload - 1.5 times rating
- Environmental - Flammability - UL V0
- Environmental - Operating temperatures - Maximum continuous 60°C
- minimum -20°C (without impact)
- Mechanical - Terminal accommodation - Back and side wire: #14 AWG min. - #12 AWG max. solid and stranded copper wire only
- push wire: #14 AWG solid copper wire only

General

Catalog Number	RSD315GY
EU RoHS Indicator	Yes
Specifications	• Base and body - PVC • Contacts - Copper alloy • Mounting strap - Galvanized steel • Rocker - Polycarbonate

UPC

- Terminal screws - Steel
 - Terminals - Brass
- 883778101267

Certifications And Compliance

Industry Standard(s)	• CSA Certified • UL Listed E3896
----------------------	---

Logistics

Carton Quantity	10
Pallet Quantity	9000

Product Assets

[Catalog Page - WDK Z-3 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Engineering Drawing - RSD315GY AutoCAD Drawing](#)
[Sales Drawings - WDK_RSD315_DRAWING_PDF](#)
[Specifications - RSD315GY Specification Sheet French](#)
[Specifications - WIRING_RSD315GY_spec](#)
[Specifications - RSD315GY Specification Sheet](#)
[Warranty - tradeSELECT™ and netSELECT®](#)
[Video - Tradeselect Devices](#)
[Video - Tradeselect Devices](#)