

Recessed 10" Series, Sub Plate,
Center, Two Gang, (1) 2.16" Opening

By Hubbell Wiring Device-Kellems
Catalog # [S1R10CSPE](#)

Fire Rated Poke Throughs, Recessed 10" Series, Sub Plate,
Center, Two Gang, (1) 2.16" Opening

Features

- Steel Construction
- White Powder Coat Paint
- Includes Necessary Mounting Hardware


Application

10" Fire-Rated Poke-Through Series

General

Accessory Type	Center Sub Plate
Application - For Use On	Concrete
Catalog Number	S1R10CSPE
Construction	Fabricated
Construction Material - Main	10 Meunt
EU RoHS Indicator	Contact Manufacturer
Finish Type	White Paint
Item Type	10" Recessed Fire-Rated Poke-Through Components
Material	Steel
Mounting Type	Screw Mount
Number Of Outlets	(1) 2.16" Opening
Size	Standard Sized Product
Style	Sub-Plates
Sub Brand	SystemOne Recessed
Type	10" Recessed Rated Poke Through Sub Plates
UPC	783585547701

Conductor Related



Cable EntryThrough Cover

Certifications And Compliance

Industry Standard(s)cULus Listed

Logistics

Carton Quantity25

Product Assets

- [BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-S1R10](#)
- [Catalog Page - WDK P-9 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - 10 INCH RECESSED FRPTAutoCAD Drawing](#)
- [Engineering Drawing - S1R10CSPE AutoCAD Drawing](#)
- [Installation Manuals - PD2815](#)
- [Literature - Hubbell SystemOne 10 Inch Fire-Rated Poke-Throughs](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Sales Drawings - WDK_S1R10PT_DRAWING_PDF](#)
- [Specifications - Wiring S1R10CSPE Specification Sheet](#)
- [Specifications - S1R10CSPE Specification Sheet English](#)
- [Specifications - S1R10CSPE Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SystemOne 10" FRPT](#)
- [Video - SystemOne 10" FRPT](#)