

Recessed 10" Series, Sub Plate,
Center, Four Gang, (4) Style Line/
Decorator Openings

By Hubbell Wiring Device-Kellems
Catalog # [S1R10CSPP](#)

Fire Rated Poke Throughs, Recessed 10" Series, Sub Plate,
Center, Four Gang, (4) Style Line®/ Decorator Openings

Features


- Steel Construction
- White Powder Coat Paint
- Includes Necessary Mounting Hardware

Application

10" Fire-Rated Poke-Through Series

General

Accessory Type	Center Sub Plate
Application - For Use On	Concrete
Catalog Number	S1R10CSPP
Construction	Fabricated
Construction Material - Main	10 Meunt
EU RoHS Indicator	Contact Manufacturer
Finish Type	White Paint
Item Type	10" Recessed Fire-Rated Poke-Through Components
Material	Steel
Mounting Type	Screw Mount
Number Of Outlets	(4) Style Line/ Decorator Openings
Size	Standard Sized Product
Style	Sub-Plates
Sub Brand	SystemOne Recessed
Type	10" Recessed Rated Poke Through Sub Plates
UPC	783585547732



Conductor Related

Cable Entry Through Cover

Certifications And Compliance

Industry Standard(s) cULus Listed

Logistics

Carton Quantity 15

Product Assets

- [BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-S1R10](#)
- [Catalog Page - WDK P-9 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - 10 INCH RECESSED FRPTAutoCAD Drawing](#)
- [Engineering Drawing - S1R10CSPP AutoCAD Drawing](#)
- [Installation Manuals - PD2815](#)
- [Literature - Hubbell SystemOne 10 Inch Fire-Rated Poke-Throughs](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Sales Drawings - WDK_S1R10PT_DRAWING_PDF](#)
- [Specifications - S1R10CSPP Specification Sheet English](#)
- [Specifications - S1R10CSPP Specification Sheet French](#)
- [Specifications - Wiring S1R10CSPP Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SystemOne 10" FRPT](#)
- [Video - SystemOne 10" FRPT](#)

