

Recessed 10" Series, Sub Plate,
Center, Three Gang, NEMA Spacing,
(3) Style Line/ Decorator Openings

By Hubbell Wiring Device-Kellems
Catalog # [S1R10CSPT](#)

Fire Rated Poke Throughs, Recessed 10" Series, Sub Plate,
Center, Three Gang, NEMA Spacing, (3) Style Line/ Decorator
Openings

Features


- Steel Construction
- White Powder Coat Paint
- Includes Necessary Mounting Hardware

Application

10" Fire-Rated Poke-Through Series

General

Accessory Type	Center Sub Plate
Application - For Use On	Concrete
Catalog Number	S1R10CSPT
Construction	Fabricated
Construction Material - Main	10 Meunt
EU RoHS Indicator	Contact Manufacturer
Finish Type	White Paint
Item Type	10" Recessed Fire-Rated Poke-Through Components
Material	Steel
Mounting Type	Screw Mount
Number Of Outlets	NEMA Spacing, (3) Style Line/Decorator Openings
Size	Standard Sized Product
Style	Sub-Plates
Sub Brand	SystemOne Recessed
Type	10" Recessed Rated Poke Through Sub Plates



UPC783585547725

Conductor Related

Cable EntryThrough Cover

Certifications And Compliance

Industry Standard(s)cULus Listed

Product Assets

- [BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-S1R10](#)
- [Catalog Page - WDK P-9 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - 10 INCH RECESSED FRPTAutoCAD Drawing](#)
- [Engineering Drawing - S1R10CSPT AutoCAD Drawing](#)
- [Installation Manuals - PD2815](#)
- [Literature - Hubbell SystemOne 10 Inch Fire-Rated Poke-Throughs](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Sales Drawings - WDK_S1R10PT_DRAWING_PDF](#)
- [Specifications - S1R10CSPT Specification Sheet French](#)
- [Specifications - Wiring S1R10CSPT Specification Sheet](#)
- [Specifications - S1R10CSPT Specification Sheet English](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SystemOne 10" FRPT](#)
- [Video - SystemOne 10" FRPT](#)

