

Recessed 6" Series, Kit

By Hubbell Wiring Device-Kellems
Catalog # [SIR6PTDEHALU](#)

Recessed 6" Series, Kit, (1) SIR6PTFIT fitting; (1) SIR6CVRALU Aluminum Recessed Cover; (1) SIR6SPD Sub Plate; (1) SIR6SPE Sub Plate; (1) SIR6SPH Sub Plate; (1) SIR6DIV Low Voltage Divider and (1) SIFRPT Hubbell Junction Box

Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

Application

6" Fire-Rated Poke-Through Series

Specifications

EU RoHS Indicator	Contact Manufacturer
Industry Standard(s)	• cULus Listed • Meets ADA Standards • UL 514A Listed

Conductor

Cable Entry	Through Cover
-------------	---------------

Configuration

Number Of Outlets	(2) 50% Left Side Sub Plates- (3) iSTATION Opening, (1) Style Line® Decorator Opening, (2) Hubbell Keystone Openings and (1) 50% Right Side- (4)
-------------------	--



20A Pre-Wired Receptacles, 1 or 2 Circuits, 18" Leads

Dimensions

Size	Standard Sized Product
------	------------------------

General

Application - For Use On	Concrete
Color	Aluminum
Style	FRPT - Complete Kits
Mounting Type	6" Core Hole
UPC	783585443225
Type	6" Recessed Rated Poke Through Kit
Material - Mounting Hardware	Mounting Hardware Included
Material	Fabricated

Logistics

Pallet Quantity	48
Carton Quantity	1

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Installation Manual \[Spanish, French, English\]](#)