

Recessed 6" Series, Through Floor
Fitting With (1) S1FRPT Hubbell
Junction Box Only, No Sub Plates

By Hubbell Wiring Device-Kellems
Catalog # [S1R6PTFIT](#)

Fire Rated Poke Throughs, Recessed 6" Series, Through Floor
Fitting With Junction Box Only, No Sub Plates

Features

- For use with a 6.00" to 6.12" Drilled or Formed Concrete Round Hole
- Up to 2 Hour Fire Rating
- Step Down Installation

General

Accessory Type	6" FRPT
Application - For Use On	Concrete
Catalog Number	S1R6PTFIT
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Item Type	6" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Size	Standard Sized Product
Specifications	<ul style="list-style-type: none">• Fire Resistance Rating - 2-Hrs. (D900)• Floor thickness - 2 1/4 in. (57.2)• Max. Cu Cross Section - 3/4 in. Power EMT .0307 sq. in.• Mounting - 6 in. (152.4)
Style	FRPT Kits
UPC	783585443188

Conductor Related

Cable Entry	Through Cover
-------------	---------------

Certifications And Compliance

Industry Standard(s)	cULus Listed
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	1
Pallet Quantity	64

Product Assets

- [BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-S1R6](#)
- [Catalog Page - WDK P-18 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - S1R6PTFIT AutoCAD Drawing](#)
- [Engineering Drawing - 6 INCH RECESSED FRPT AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2837_PD2462_INSTALLINST](#)
- [Literature - Hubbell SystemOne 4, 6 and 8 Inch Recessed Fire-Rated Poke-Throughs](#)
- [Literature - Installation Efficient Product Solutions](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Delivery Systems Product Guide](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Sales Drawings - WDK_S1R6PT_DRAWING_PDF](#)
- [Sales Drawings - WDK_S1R6_DRAWING_PDF](#)
- [Specifications - Wiring S1R6PTFIT Specification Sheet](#)
- [Specifications - S1R6PTFIT Specification Sheet](#)
- [Specifications - S1R6PTFIT Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)

