

Recessed 8" Series, Replacement
Fitting Box, (1) 1- 1/4" EMT and (1)
2" EMT

By Hubbell Wiring Device-Kellems
Catalog # [S1R8JNC10](#)

Fire Rated Poke Throughs, Recessed 8" Series, Replacement
Fitting Box, (1) 1-1/4" EMT and (1) 2" EMT

Features

- S1R8PTFIT Center Chamber Fitting Box
- Includes Mounting Hardware and (1) Fitting Box Divider

Application

8" Fire-Rated Poke-Through Series

General

Accessory Type	Fitting Plates & Boxes
Application - For Use On	Concrete
Catalog Number	S1R8JNC10
EU RoHS Indicator	Contact Manufacturer
Finish Type	Natural
Item Type	8" Recessed Fire-Rated Poke-Through Components
Material	Fabricated
Material - Mounting Hardware	Mounting Hardware Included
Mounting Type	Screw Mount
Size	Standard Sized Product
Style	Accessories
Type	8" Recessed Rated Poke Through Accessories
UPC	783585548708

Conductor Related

Cable Entry	Through Cover
-------------	---------------



Certifications And Compliance

Industry Standard(s)	cULus Listed
----------------------	--------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-S1R8_JNC3](#)
- [BIM - Electrical_Equipment-Poke_Through-Hubbell_Wiring-System_One-S1R8](#)
- [Catalog Page - WDK P-14 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - 8 INCH RECESSED FRPT AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2463_INSTALLINST](#)
- [Literature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
- [Sales Drawings - WDK_S1R8JNC_DRAWING_PDF](#)
- [Sales Drawings - WDK_S1R8PT_DRAWING_PDF](#)
- [Specifications - S1R8JNC10 Specification Sheet](#)
- [Specifications - S1R8JNC10 Specification Sheet](#)
- [Specifications - S1R8JNC10 Specification Sheet French](#)
- [Specifications - Wiring S1R8JNC10 Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)

