

Temporary Power Products, Spider
Portable Power, Complete Unit,
Straight Blade Style, With 7) 20A
125V Receptacles- 1) 30A 125/250V
Inlet and Outlet

By Hubbell Wiring Device-Kellems
Catalog # [SDSB1A](#)

Temporary Power Products, Spider Portable Power, Complete
Unit, Straight Blade Style, With 7) 20A 125V Receptacles- 1) 30A
125/250V Inlet and Outlet, Yellow

Features

- Individual GFCI modules
- TYPE 3R metallic enclosure and heavy duty,abuse resistant legs
- Standard stab termination circuit breakers with gasketed lift cover

Application

Heavy Duty Portable

Performance

Environment - Moisture Resistance - Indoor and outdoor wet and dry locations

General

Catalog Number	SDSB1A
EU RoHS Indicator	No
Environmental Conditions	Indoor and Outdoor
Item Type	Straight Blade Singles
Material	Thermoplastic
Material - Mounting Hardware	Non-Mounted, Portable
Number Of Poles	2-Pole
Series	Spider II
Specifications	• Code Compliance - NEC®, ANSI/NFPA 70 • Enclosure Type - 3R, rainproof, suitable for use in damp locations
Type	7-20A, 125V Straight Blade Receptacles, 1-30A 125/250V Inlet and Outlet, Yellow
UPC	783585370897



Dimensions

Display Size	Standard Sized Product
--------------	------------------------

Electrical Ratings

Amperage Rating	50 A
Connectivity	Pre-Wired
Current / Amperage Rating	50 A
Current Rating	60 A
Phase	Three Phase
Voltage Rating	120/240 VAC
Voltage Rating Description	120/240 VAC
Wattage	12480

Conductor Related

Number Of Wires	3-Wire Grounding
-----------------	------------------

Certifications And Compliance

Industry Standard(s)	UL 1640 cUL and CSA, UL 943
Nema Rating	6) 5-20R, 1) L15-30R

Product Assets

[Catalog Page - WDK H-12 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD1989_INSTALLINST](#)
[Literature - Safety Product Guide](#)
[Literature - Education Application Guide](#)
[Literature - Entertainment Product Solution Guide](#)
[Sales Drawings - WDK_SDSB1A_DRAWING_PDF](#)
[Specifications - SDSB1A Specification Sheet](#)
[Specifications - Wiring SDSB1A Specification Sheet](#)
[Specifications - SDSB1A Specification Sheet French](#)
[Warranty - Industrial & Commercial Products](#)