

Industrial Grade, Lever Actuated, Switched
Twist-Lock Enclosure With pre-wired
HBL2730 Receptacle, 30A Twist-Lock®, 3
Phase 480 V AC, NEMA L16-30R.

By Hubbell Wiring Device-Kellems
Catalog # [SE2730A](#)

Switches and Lighting Controls, Industrial Grade, Lever Actuated,
Switched Twist-Lock Enclosure With pre-wired HBL2730
Receptacle, 30A Twist-Lock®, 3 Phase 480 V AC, NEMA L16-30R,
Terminal Screws, Gray.

Features

- Lockable handle provides lockout protection for greater safety and complies with OSHA lockout requirements
- Horsepower rated switch
- Large receptacle gasketless door and hinge assembly
- Heavy-duty internal frame bonds conduit and all grounds and has a DIN rail to accommodate the switch

Performance

Electrical - Current Interrupting - Certified for current interrupting at full rated current and voltage, Electrical - Dielectric Voltage - Withstands 3,000V minimum, Electrical - Max. Working Voltage - 600V RMS, Electrical - Operations - Mechanical 10,000 cycles, Electrical 6,000 cycles, Environmental - Flammability - UL94 - 5 VA and VO classification, Environmental - Moisture Resistance - IP54 suitability, Environmental - Operating Temperature - Maximum continuous +75°C Minimum continuous -40°C, Environmental - UV Resistance - All materials are UV stabilized, Mechanical - Impact Resistance - In accordance with UL 746C, Mechanical - Mounting - External fully adjustable feet, Mechanical - Product Identification - Identification and ratings are part of external label and receptacle face, Mechanical - Terminal Identification - In accordance with UL, CSA and international conventions

Specifications

EU RoHS Indicator	No
Nema Rating	L16-30R
Industry Standard(s)	• CSA Certified Type 3R and 12K Enclosure Rating • Listed to UL Standard

Current

Voltage Rating Description	3 Phase 480 VAC
Dielectric Strength	Withstands 3,000V minimum



Voltage Rating	3 Phase 480 VAC
----------------	-----------------

Dimensions

Length	11.38 in
Weight	4 lb.
Height	4.38 in
Width	4.88 in
Dimensions	11.38 in x 4.88 in x 4.38 in

General

Color	Gray
Specifications	• Base - PBT • Conduit Hub - Zinc ¾" watertight • Enclosure Gasket - Neoprene • Handle - PBT • Shaft - PBT • Top - PBT
UPC	783585006352
Type	Switched Enclosure
Item Type	Switched Safety Enclosures

Logistics

Carton Quantity	1
-----------------	---

Operational

Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Horsepower - Maximum	10

Product Assets

[Catalog \[English\]](#)
[Catalog Page \[English\]](#)
[Installation Manual \[English\]](#)