

Kellems Wire Management, Cord
Connectors, European Style, .87-
1.3", 40MM, Black

By Hubbell Wiring Device-Kellems
Catalog # [SECM40B](#)

Kellems Wire Management, Cord Connectors, European Style,
.87-1.3", 40MM, Black

Features

- Low profile
- Connector body is a one-piece design with machined threads

Application

Straight Male Connector

Performance

- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperatures - -22°F to 225°F (-30°C to 107°C)
- Environmental - Protection Class - IP66 Suitability

General

Catalog Number	SECM40B
EU RoHS Indicator	Yes
Environmental Conditions	Suitable For Use In Wet Locations When Used With A Listed Nylon Washer Between Box And Fitting.
Item Type	Low Profile Cord Connectors
Material	Non-Metallic
Material - Mounting Hardware	Locknut or Tapped Opening
Series	Low Profile Metric
Specifications	<ul style="list-style-type: none">• Body - Nylon• Cord Diameter Inches (mm) - .87"-1.30" (22.0-32.0)• Gland - Buna N• Hub Size - M40
Temperature Rating	Minimum -22 Deg F to 225 Deg F (-30 Deg C to 107 Deg C)
Type	Connector
UPC	783585018614



Dimensions

Display Size	40mm
Hub Size	M40

Conductor Related

Conductor Range	0.87-1.3 in (22.0-32.0 mm)
Number of Conductors	Single

Certifications And Compliance

Industry Standard(s)	UL Listed
Nema Rating	IP66

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK W-74 Catalog Page](#)
[Catalog Page - WDK W-73 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Literature - PULP & PAPER SOLUTIONS](#)
[Literature - Pulp & Paper Solutions](#)
[Literature - FOOD & BEVERAGE SOLUTIONS](#)
[Sales Drawings - WDK_SECM40B_DRAWING_PDF](#)
[Specifications - SECM40B Specification Sheet](#)
[Specifications - SECM40B Specification Sheet French](#)
[Specifications - Wiring SECM40B Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)
[Video - Kellems Wire Management Solutions](#)
[Video - Kellems Wire Management Solutions](#)