



Switches and Lighting Controls, Industrial/Commercial Grade, SNAPConnect Series, Toggle Switches, Single Pole, 15A 120/277V AC Toggle, North American

By Hubbell Wiring Device-Kellems
Catalog # [SNAP1201WNA](#)



Industrial/Commercial Grade, SNAP-Connect Series Toggle
Switch Single-Pole, 15A 120/277V AC Toggle, North American.

Features

- Steel, zinc plated bridge is corrosion resistant
- Thread cleaning captive mounting screw
- Automatic self-grounding staple assures continuity to wall box

General

Color	<ul style="list-style-type: none"> • White • Blanc
Item Type	Single Pole Toggle Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without impact
Performance	<ul style="list-style-type: none"> • Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute • Electrical - Max. Continuous Current - 15A • Electrical - Max. Working Voltage - 277V AC • Electrical - Overload - Minimum 4.8 times rated current for 100 cycles • Electrical - Temperature Rise - 30°C maximum at rated current • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact • Mechanical - Terminal Accommodations - Uses SNAPConnect Connector
Series	General Purpose

Dimensions

Dimensions	4.18 in x 1.3 in x 1.74 in
Height	1.74 in
Length	4.18 in
Width	1.3 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Certifications and Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK D-8 Catalog Page](#)
- [Catalog Page - WDK X-15 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - SNAP1201WNA AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2403_INSTALLINST](#)
- [Literature - Healthcare Product Solutions](#)
- [Literature - Healthcare Application Guide](#)
- [Literature - Installation Efficient Product Solutions](#)
- [Literature - SNAPConnect® Devices](#)
- [Literature - Emergency Preparedness for Healthcare](#)
- [Sales Drawings - WDK_SNAP1201_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SNAPConnect Devices](#)

Style
Type

Single Pole
• Toggle
• Toggle

UPC

783585186450



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-SNAP1201WNA-SPEC-EN | REV 1/2024