



Straight Blade Devices, Receptacles, Decorator, Duplex, Commercial/Industrial Grade, SNAPConnect, Two USB type 2.0 ports 3 Amp 5 Volt, 15A 125V AC

By Hubbell Wiring Device-Kellems
Catalog # [SNAP15USB1](#)



Straight Blade Devices, Receptacles, Decorator, Duplex, Commercial/Industrial Grade, SNAPConnect, Two USB type 2.0 ports 3 Amp 5 Volt, 15A 125V AC, 2-Pole 3-Wire Grounding, 5-15R, Ivory.

Features

- Two USB ports 3 Amp, 5V DC, type A, class 2.0
- Tamper-Resistant decorator duplex receptacle
- Green LED indicator to show USB power available
- Compatible with USB 1.1/2.0/3.0 devices, including Apple® products

Application

Extra Heavy Duty

General

Color	<ul style="list-style-type: none"> • Ivory • Ivoire
Horsepower - Maximum	0.5
Indicator(s) Type	Green LED
Item Type	SNAPConnect USB Charger Style Line Decorator Duplex Receptacle
Number Of Poles	2-Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Performance	<ul style="list-style-type: none"> • Electrical - Current Interrupting - Receptacle certified for current interrupting at full rated current • Electrical - Dielectric Voltage - Withstands 2,000V minimum • Environmental - Flammability - UL 94V-2 • Environmental - Operating Temperature - Maximum continuous 75°C, minimum -40°C (w/o impact) • Mechanical - Product Identification - Ratings are a permanent part of the device

Dimensions

Dimensions	3.28 in x 1.75 in x 1.54 in
Height	1.54 in
Length	3.28 in
Width	1.75 in

Electrical Ratings

Amperage Rating	15 A
Current / Amperage Rating	15 A
Current Rating	15 A
Dielectric Strength	Withstands 2,000V minimum
Voltage Rating	125 V
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14 AWG to #10 AWG

Certifications and Compliance

Industry Standard(s)	cETLus Listed to UL498
Nema Rating	5-15R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2023](#)
- [Engineering Drawing - SNAP15USB1 AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2603_INSTALLINST](#)
- [Sales Drawings - WDK_SNAP15USB_DRAWING_PDF](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - SNAPConnect Devices](#)
- [Video - Tamper-Resistant Receptacles](#)

- Mechanical - Terminal Accommodation - #14-#10 AWG copper stranded or solid conductor only
- Mechanical - Terminal Identification - Terminals identified in accordance with UL 498 and CSA
- Mechanical - USB Port - Stainless steel Rated for 10,000 plug insertions and removal

Series

USB Charger

Style

Style Line Decorator

Type

- Tamper-Resistant
- Tamper-Resistant

UPC

883778305368



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-SNAP15USBI-SPEC-EN | REV 1/2024