

Switches and Lighting Controls,  
Industrial/Commercial Grade,  
SNAPConnect Series, Decorator  
Switches, Three Way, 20A  
120/277V AC, Ivory, North  
American

By Hubbell Wiring Device-Kellems  
Catalog # [SNAP2123INA](#)

Switches and Lighting Controls, Industrial/Commercial Grade,  
SNAPConnect Series, Decorator Switches, Three Way, 20A  
120/277V AC, Ivory, North American

Features

- Steel, zinc plated bridge is corrosion resistant
- Thread cleaning captive mounting screw
- Self-grounding staple assures continuity to wall box

Application

General Purpose

Performance

- Electrical - Dielectric Voltage - Withstands 1500V AC minimum for 1 minute
- Electrical - Max. Continuous Current - 20A
- Electrical - Max. Working Voltage - 277V AC
- Electrical - Overload - Minimum 4.8 times rated current for 100 cycles
- Electrical - Temperature Rise - 30°C maximum at rated current
- Environmental - Flammability - UL 94V-2
- Environmental - Operating Temperature - Max. continuous: 75°C, Min. continuous: -40°C without impact
- Mechanical - Terminal Accommodations - Uses SNAPConnect Connector

General

Action	SPDT
Catalog Number	SNAP2123INA
EU RoHS Indicator	No
Item Type	Three Way Style Line Decorator Switch
Material	Thermoplastic
Number Of Poles	Single Pole
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Series	<ul style="list-style-type: none"><li>• SnapConnect Devices</li><li>•</li></ul>



Specifications

	<ul style="list-style-type: none"><li>• Base Material - Thermoplastic, Black</li><li>• Contacts - Silver Alloy</li><li>• Rocker Material - Thermoplastic</li><li>• Terminals - Brass</li><li>• Top Material - Thermoplastic, Red</li></ul>
Style	Three Way
Type	Rocker/Decorator
UPC	783585189857

Dimensions

Dimensions	4.28 in x 1.44 in x 1.54 in
Height	1.54 in
Length	4.28 in
Width	1.44 in

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Current Rating	20 A
Dielectric Strength	Withstands 1500V AC minimum for 1 minute
Temperature Rise - Max.	30°C maximum at rated current
Voltage Rating	120-277 VAC
Voltage Rating Description	120-277 VAC

Certifications And Compliance

Industry Standard(s)	UL Listed
----------------------	-----------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK D-9 Catalog Page](#)  
[Catalogs - WDK Catalog Full 2024](#)  
[Engineering Drawing - SNAP2123INA AutoCAD Drawing](#)  
[Installation Manuals - WIRING\\_PD2403\\_INSTALLINST](#)  
[Literature - SNAPConnect® Devices](#)  
[Sales Drawings - WDK\\_SNAP2123\\_DRAWING\\_PDF](#)

[Specifications - SNAP2123INA Specification Sheet](#)  
[Specifications - Wiring SNAP2123INA Specification Sheet](#)  
[Specifications - SNAP2123INA Specification Sheet French](#)  
[Warranty - Industrial & Commercial Products](#)  
[Video - SNAPConnect Devices](#)  
[Video - SNAPConnect Devices](#)



**A Hubbell brand**

©2025 Hubbell Incorporated. All rights reserved  
WDK\_CA-SNAP2123INA-SPEC-EN | REV 4/2025