

Wallplates and Boxes, Metallic
Plates, 1- Gang, 1) 1.40" Opening,
Standard Size, Stainless Steel

By Hubbell Wiring Device-Kellems
Catalog # [SS7](#)



Locking Devices, 50 Amp Locking Accessories, Wallplates,
Stainless Steel 302/304, 1- Gang.

Features

- Used with Single Receptacles with Face Dia. 1.40" (35.6)

General

Catalog Number	SS7
Color	Stainless Steel
Construction	Stamped
Cutout	1) 1.40" Opening
EU RoHS Indicator	Yes
Item Type	Wallplates, 1-Gang
Material	Stainless Steel
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	-40°C to 85 °C
Orientation	Vertical Mount
Size	1-Gang
Specifications	- Appearance - Horizontal brushed finish - Mounting Screws - 302/304 SS, Slotted Head - Plate Material - Stainless steel 302/304 - Plate Openings - Single Receptacle - Plate Type - Wall Plate
Style	Horizontal Brushed Finish
UPC	883778201103

Dimensions

Display Size	Standard Sized
Thickness	0.035
Weight	0.15 lb

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	13200

Product Assets

[Catalog Page - WDK A-52](#) [Catalog Page - WDK B-62](#) [Catalog Page - WDK O-39](#) [Catalog Page - WDK N-7](#) [Catalog Page - WDK B-50](#) [Catalog Page - WDK AA-45](#) [Catalog Page - WDK N-18](#) [Catalog Page - WDK B-63](#) [Catalogs - WDK Catalog Full 2024](#) [Literature - Hubbell Marine Full Line Catalog](#) [Specifications - SS7 Specification Sheet](#) [Specifications - Wiring SS7 Specification Sheet](#) [Specifications - SS7 Specification Sheet French](#) [Warranty - Industrial & Commercial Products](#)