

Wallplates and Boxes, Metallic
Plates, 1- Gang, 1) 1.70" Opening,
Standard Size, Stainless Steel

By Hubbell Wiring Device-Kellems
Catalog # [SS725](#)



Twist-Lock® Devices, Receptacle Wallplates, Stainless steel
302/304, .035 in. (0.9), horizontal brushed finish

Features

- Used with Single Receptacles with Face Dia. 1.74" (44.2)

General

Catalog Number	SS725
Color	Stainless Steel
Construction	Stamped
Cutout	1) 1.70" Opening
EU RoHS Indicator	Yes
Item Type	Receptacle Wallplates
Material	Stainless Steel, Type 302/304
Material - Mounting Hardware	Screw Mounting
Number of Gang(s)	1-Gang
Operating Temperature	Maximum continuous 75°C and minimum -40°C without Impact
Orientation	Vertical Mount
Size	Standard
Specifications	• Appearance - Horizontal brushed appearance • Mounting Screws - 302/304 Stainless Steel, Slotted head • Plate Material - Stainless steel 302/304 • Plate Openings - 1-Single • Plate Type - 1-Gang
Style	1-Single - 1.74 in. Hole
UPC	883778201189

Dimensions

Display Size	Standard Sized
Thickness	0.035
Weight	0.1 lb

Certifications And Compliance

Industry Standard(s)	UL Listed
Standards - RoHS Compliance	CM
Status	

Logistics

Carton Quantity	10
Pallet Quantity	13200

Product Assets

[Catalog Page - WDK B-49 Catalog Page](#)
[Catalog Page - WDK AA-11 Catalog Page](#)
[Catalog Page - WDK N-18 Catalog Page](#)
[Catalog Page - WDK N-8 Catalog Page](#)
[Catalogs - WDK Catalog Full 2024](#)
[Literature - Hubbell Marine Full Line Catalog](#)
[Specifications - SS725 Specification Sheet](#)
[Specifications - SS725 Specification Sheet French](#)
[Specifications - Wiring SS725 Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)