

Temporary Power Products, Spider II Portable Power, Replacement Parts, Supervisory Kit, 50A

By Hubbell Wiring Device-Kellems
Catalog # [SSK](#)



Temporary Power Spider II Portable Power, Replacement Supervisory Kit, 50A

Features

- Spider II Portable Power
- Replacement Parts
- Supervisory Kit
- 50A

Application

Temporary Power Distribution

General

Catalog Number	SSK
EU RoHS Indicator	No
Environmental Conditions	Indoor/Outdoor
Material	Thermoplastic
Number Of Poles	2-Pole
Specifications	<ul style="list-style-type: none">• Code Compliance - NEC®, ANSI/NFPA 70• Enclosure Type - 3R, rainproof, suitable for use in damp locations• Environment - Moisture Resistance
Style	Spider Supervisory Kit
Type	Replacement Part
UPC	783585369570

Dimensions

Display SizeStandard Sized Product

Electrical Ratings

Amperage Rating	50 A
Current / Amperage Rating	50 A
Phase	Single Phase

Conductor Related

Number Of Wires	3-Wire Grounding
-----------------	------------------

Certifications And Compliance

Industry Standard(s)	UL 1640 cUL and CSA, UL 943
Nema Rating	Non-NEMA

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK H-13 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - PULP & PAPER SOLUTIONS](#)
- [Literature - Pulp & Paper Solutions](#)
- [Specifications - SSK Specification Sheet French](#)
- [Specifications - SSK Specification Sheet](#)
- [Specifications - Wiring SSK Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)