



USB Charger Duplex Receptacle, 15A 125V, 2-Pole 3-Wire Grounding, 5-15R, 2) 5A USB Ports, Gray

By Hubbell Wiring Device-Kellems
Catalog # [USB15A5GY](#)

USB Charger Duplex Receptacle, 15A 125V,2-Pole 3-Wire
Grounding, 5-15R, 2) 5A USB Ports, Gray.



Features

- High Power 5 Amp, 5 Volt USB Output
- Two Type A USB Ports
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

General

Color	<ul style="list-style-type: none">• Gray• Gris
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Style Line Decorator
Type	<ul style="list-style-type: none">• Two Type A USB Ports• Two Type A Port
UPC	883778306914

Electrical Ratings

Current / Amperage Rating	15 A
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications and Compliance

Nema Rating	5-15R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalog Page - WDK Z-7 Catalog Page](#)
[Catalog Page - WDK A-31 Catalog Page](#)
[Catalogs - WDK Catalog Full 2023](#)
[Engineering Drawing - USB15A5GY AutoCAD Drawing](#)
[Installation Manuals - WIRING_PD2705_INSTALLINST](#)
[Sales Drawings - WDK_USB15A5_DRAWING_PDF](#)
[Warranty - Industrial & Commercial Products](#)



A proud member of the Hubbell Family.

©2024 Hubbell Incorporated. All rights reserved.
WDK_CA-USB15A5GY-SPEC-EN | REV 1/2024