

USB Charger Duplex Receptacle,
20A 125V, 2-Pole 3-Wire Grounding

By Hubbell Wiring Device-Kellems
Catalog # [USB20ACW](#)

USB Charger Duplex Receptacle, 20A 125V,2-Pole 3-Wire
Grounding, 5-20R, 1) 3.1 A "C" USB and "A" Ports, White



Features

- High Power 3.1 Amp, 5 Volt USB Output
- One Type A Port, One Type-C Port
- Tamper Resistant Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

General

Catalog Number	USB20ACW
Insulation	N/A
Material	Composite
Mounting Method	Mounting Screws
Number Of Poles	2-Pole
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Style Line Decorator
Temperature Rating	Maximum continuous 75°C, minimum -40°C (w/o impact)
UPC	883778310119

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Dielectric Strength	1500 V Withstand
Phase	Single Phase
Voltage Rating	125 V
Wattage	1815 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14-10 AWG

Certifications And Compliance

Industry Standard(s)	cULus Listed to UL498, UL1310
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Installation Manuals - WIRING_PD2895_INSTALLINST](#)
[Literature - Multifamily Property Tech Enhancements](#)
[Literature - Residential Catalog](#)
[Literature - Differentiate Your Property](#)
[Literature - Property Management | Home Enhancements | Innovation and Convenience](#)
[Sales Drawings - WIRING_M14078_SALESDRAWING](#)
[Specifications - WIRING_USB20ACW_spec](#)
[Specifications - USB20ACW Specification Sheet French](#)
[Specifications - USB20ACW Specification Sheet](#)
[Warranty - Industrial & Commercial Products](#)