

USB Charger Duplex Receptacle,
20A 125V, 2-Pole 3-Wire Grounding

By Hubbell Wiring Device-Kellems
Catalog # [USB20AI](#)

USB Charger Duplex Receptacle, 20A 125V,2-Pole 3-Wire
Grounding, 5-20R, 2) 3.1 A USB Ports, Brown



Application

USB Charging/Power

General

Catalog Number	USB20AI
EU RoHS Indicator	Contact Manufacturer
Environmental Conditions	Indoor Dry Unless Protected by Additional Means
Insulation	N/A
Material	Composite
Mounting Method	Mounting Screws
Number Of Poles	2-Pole
Series	Hubbell-PRO
Size	Standard Sized Product
Style	Style Line Decorator
Temperature Rating	Maximum continuous 75°C, minimum -40°C (w/o impact)
Type	Two Type A USB Ports
UPC	883778310041

Electrical Ratings

Amperage Rating	20 A
Current / Amperage Rating	20 A
Dielectric Strength	1500 V Withstand
Phase	Single Phase

Voltage Rating	125 V
Wattage	1815 W

Conductor Related

Number Of Wires	3-Wire
Wire Size	#14-10 AWG

Certifications And Compliance

Industry Standard(s)	cULus Listed to UL498, UL1310
Nema Rating	5-20R

Logistics

Carton Quantity	10
Pallet Quantity	3500

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - WIRING_PD2895_INSTALLINST](#)
- [Literature - Residential Catalog](#)
- [Sales Drawings - WIRING_M14078_SALESDRAWING](#)
- [Specifications - USB20AI Specification Sheet](#)
- [Specifications - USB20AI Specification Sheet French](#)
- [Specifications - WIRING_USB20AI_spec](#)
- [Warranty - Industrial & Commercial Products](#)