

USB Charger Duplex Receptacle,
20A 125V, 2-Pole 3-Wire Grounding,
5-20R, 2) 5A "C" USB Ports, Ivory

By Hubbell Wiring Device-Kellems
Catalog # [USB20C5I](#)

USB Charger Duplex Receptacle, 20A 125V,2-Pole 3-Wire
Grounding, 5-20R, 2) 5A "C" USB Ports, Ivory

General

Catalog Number	USB20C5I
EU RoHS Indicator	Contact Manufacturer
Number Of Poles	2-Pole
Series	Heavy Duty
Style	Style Line Decorator
Type	Two Type-C Port
UPC	883778307515

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating Description	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance

Nema Rating	5-20R
-------------	-------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Z-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - USB20C5I AutoCAD Drawing](#)
- [Installation Manuals - WIRING_PD2705_INSTALLINST](#)
- [Literature - USB Charging Receptacles](#)
- [Literature - USB Charging Centers](#)
- [Literature - Residential Product Guide](#)
- [Literature - Entertainment Product Solution Guide](#)
- [Sales Drawings - WDK_USB20C5_DRAWING_PDF](#)
- [Specifications - USB20C5I Specification Sheet](#)
- [Specifications - USB20C5I Specification Sheet French](#)
- [Specifications - Wiring USB20C5I Specification Sheet](#)
- [Warranty - Industrial & Commercial Products](#)

