

USB Charger Receptacle, 20A 125V
Duplex, Power Delivery 55W Type C
Ports, NEMA 5-20R, Black

By Hubbell Wiring Device-Kellems
Catalog # [USB20CPDBK](#)

Tamper Resistant Receptacle, 2-Pole 3-Wire Grounding, 1 Type
"C" Power Delivery, 1 Type "C" Standard 5V

Features

- High Power 55 Watt USB Power Delivery 3.0 Standard, 5 Volt USB BC1.2 Output
- Two Type C USB Ports, One Supports Power Delivery
- Tamper Resistant Commercial Grade Duplex Compatible
- USB Ports Rated 10,000 Cycles

General

Catalog Number	USB20CPDBK
Color	Black
Number Of Poles	2-Pole
Series	USB Charger
Style	Style Line Decorator
Type	Tamper Resistant USB
UPC	783585723228

Electrical Ratings

Current / Amperage Rating	20 A
Voltage Rating	125 V

Conductor Related

Number Of Wires	3-Wire
-----------------	--------

Certifications And Compliance



Industry Standard(s)	NEMA 5-20R, USB PD 3.0, USB BC1.2
Nema Rating	5-20R

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Brochures - WDK USB Receptacle CA - English](#)
- [Brochures - WDK USB Receptacle CA - French](#)
- [Catalog Page - WDK Q-4 Catalog Page](#)
- [Catalog Page - WDK A-32 Catalog Page](#)
- [Catalog Page - WDK Z-7 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Installation Manuals - PD3040](#)
- [Literature - FREQUENTLY ANSWERED QUESTIONS USB-C Power Delivery Receptacles](#)
- [Literature - USB Power Delivery Receptacles](#)
- [Literature - WDK USB Receptacle FAQ Canada - English](#)
- [Literature - WDK USB Receptacle FAQ Canada - French](#)
- [Sales Drawings - M-14671](#)
- [Specifications - USB20CPDBK Specification Sheet](#)
- [Specifications - WIRING_USB20CPDBK_spec](#)
- [Specifications - USB20CPDBK Specification Sheet French](#)
- [Warranty - Industrial & Commercial Products](#)
- [Video - Hubbell USB-C PD Receptacles](#)