

Prise double pour chargeur USB, qualité hôpital, 15A 125V, 2 pôles, 3 fils, mise à la terre, 5-15R, 1) 5A USB "C" et ports "A", blanc

Par Hubbell Wiring Device-Kellems
No de catalogue [USB8200AC5W](#)

Prise double pour chargeur USB, qualité hôpital, 15A 125V, 2 pôles, 3 fils, mise à la terre, 5-15R, 1) USB "C" 5A et ports "A", blanc.



Général

Numéro de catalogue	USB8200AC5W
Couleur	
Indicateur RoHS de l'UE	Contacter le fabricant
Nombre de pôles	2 pôles
Série	Classe d'hôpital
Style	Décorateur de lignes de style
Type	Un port de type A, un port de type C
CUP	883778307317

Caractéristiques électriques

Courant / Intensité nominale	15 A
Tension nominale Description	125 V

Chef d'orchestre

Nombre de fils	3 fils
----------------	--------

Certifications et conformité

Nema Rating	5-15R
-------------	-------

Logistique

Quantité de cartons	10
---------------------	----

Documentation

[Catalogues - WDK Catalog Full 2024](#)
[Dessin technique - USB8200AC5W AutoCAD Drawing](#)
[Dessins de vente - WDK_USB8200AC5_DRAWING_PDF](#)
[Garantie - Industrial & Commercial Products](#)
[Littérature - Healthcare Product Solutions](#)
[Littérature - Duct Products Guide](#)
[Littérature - Hubbell SystemOne Recessed Fire-Rated Poke-Throughs](#)
[Littérature - Hospital Grade USB Receptacles](#)
[Littérature - Emergency Preparedness for Healthcare](#)
[Manuels d'installation - WIRING_PD2705_INSTALLINST](#)
[Page du catalogue - WDK L-10 Catalog Page](#)
[Spécifications - Wiring USB8200AC5W Specification Sheet](#)
[Spécifications - USB8200AC5W](#)

