

2X2 USB Work Surface Pop-Up Boxes

By Hubbell Wiring Device-Kellems
Catalog # [WSBUSB2X2AC5ALU](#)



2X2 USB Work Surface Pop-Up Box, 15A, 125V USB Duplex Gray Receptacle, (1) Type A & (1) Type-C USB Charging Ports, Brushed Aluminum Finish

Features

- 125V, 15A Duplex with (1) Type A & (1) Type-C USB Charging Ports
- 5A Charging Capacity
- Tamper-resistant Receptacle
- 5' pre-wired, 12 gauge, 3 wire electrical cord
- Low 0.070" Tapered Flange Height

Application

Furniture Power Distribution Units fro Maximum Surface Thickness of 1.125 Inches

General

Catalog Number	WSBUSB2X2AC5ALU
EU RoHS Indicator	Contact Manufacturer
Material	Aluminum Cover & Flange
Number Of Outlets	(1) Duplex Receptacle with (2) USB Ports
Sub Brand	Pre-Wired Work Surface Elite Series
Type	• 2X2 USB Work Surface Pop-Up Boxes • USB Type A & Type-C
UPC	783585590158

Dimensions

Cubic Capacity	1.2425 cu.in
Depth	3.55 in
Dimensions	5 in x 5 in x 0.07 in
Height	0.07 in
Length	5 in
Width	5 in

Certifications And Compliance

Industry Standard(s)	cULus listed to UL962A
----------------------	------------------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalog Page - WDK Q-5 Catalog Page](#)
- [Catalog Page - WDK X-2 Catalog Page](#)
- [Catalogs - WDK Catalog Full 2024](#)
- [Engineering Drawing - M14246_ACAD](#)
- [Installation Manuals - WIRING_PD2637_INSTALLINST](#)
- [Literature - 2X2 USB Work Surface Pop-Up Box](#)
- [Sales Drawings - M14246](#)
- [Specifications - WSBUSB2X2AC5ALU Specification Sheet](#)
- [Specifications - WSBUSB2X2AC5ALU Specification Sheet French](#)
- [Specifications - WIRING_WSBUSB2X2AC5ALU_spec](#)
- [Warranty - Industrial & Commercial Products](#)

