

YC406250

By Hubbell Wiring Device-Kellems
Catalog # [YC406250](#)

Bulk Cable, 6/4 STO, 250'



Application

Ship-To-Shore Cables

Specifications

EU RoHS Indicator	Yes
Industry Standard(s)	UL Listed

Conductor

Strands	Multi
Braid	None
Number Of Conductors	4
Conductor Type	Copper

Configuration

Debris Shield Type	None
--------------------	------

Current

Amperage Rating	50 A
Voltage Rating	600V AC Max kV

Dimensions

Outside Diameter	0.845
Weight	0.86 lb.

General

Color	Yellow
Material - Jacket	STOW- PVC
Material - Insulation	Man Made Rubber
Specifications	- Cable Rating - 50A 6 Gauge/4 Wire STO- 250' Roll - Length - 250 ft. (76.2m) - Product Type - Bulk Cable
UPC	783585831206

Logistics

Carton Quantity	250
-----------------	-----

Operational

Temperature Rating	Limited by Devices
--------------------	--------------------

Product Assets

- [Catalog \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)
- [Catalog Page \[English\]](#)