

Support Grips, Single Eye, Single Weave, Closed Mesh, Tin-Coated Bronze, 1.50-1.74"

By Hubbell Wiring Device-Kellems
Catalog # [02201019](#)

Support Grips, Single Eye, Single Weave, Closed Mesh, Tin-Coated Bronze, 1.50-1.74"



Application

- Single Eye

Performance

- Mechanical - Approximate Breaking Strength - 1,610 (7,161) Lbs. (N)
- Mechanical - Working Load - 161 (716.1) Lbs. (N)

General

| | |
|------------------------------|--|
| Approx Breaking Strength | 1,610 lbs |
| Catalog Number | 02201019 |
| Construction | Woven |
| EU RoHS Indicator | Yes |
| Material | Bronze, Tin Coated |
| Material - Mounting Hardware | Screw Hook or Beam Clamp |
| Series | Standard Duty |
| Specifications | <ul style="list-style-type: none">• Eye - Stainless Steel• Lug - Stainless Steel• Strand - Stainless Steel• Tag - Mylar |
| Style | Closed Mesh, Single Weave |

| | |
|------|--------------|
| Type | Single Eye |
| UPC | 783585301051 |

Conductor Related

| | |
|----------------------|-------------------------|
| Cable Diameter Range | 1.5 in-1.74 in |
| Cable Size | 1.50"-1.74" (3.81-4.42) |

Certifications And Compliance

| | |
|------------------------------------|---------------|
| Industry Standard(s) | CSA Certified |
| Standards - RoHS Compliance Status | CM |

Logistics

| | |
|-----------------|-----|
| Carton Quantity | 10 |
| Pallet Quantity | 900 |

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 2201019](#)
- [Warranty - Industrial & Commercial Products](#)