

Support Grips, Single Eye, Single Weave, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.25-1.49"

By Hubbell Wiring Device-Kellems
Catalog # [02202018](#)

Support Grips, Single Eye, Single Weave, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.25-1.49"



Application

- Single Eye

Performance

- Mechanical - Approximate Breaking Strength - 1,610 (7,161) Lbs. (N)
- Mechanical - Working Load - 161 (716.1) Lbs. (N)

General

Approx Breaking Strength	1,610 lbs
Catalog Number	02202018
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Equalizer - Bronze• Eye - Copper• Lace - Tin-coated bronze• Strand - Tin-coated bronze• Tag - Mylar
Style	Split Mesh, Lace Closing

Type	Single Eye
UPC	783585302225

Conductor Related

Cable Diameter Range	1.25 in-1.49 in
Cable Size	1.25"-1.49" (3.17-3.78)

Certifications And Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

Logistics

Carton Quantity	10
Pallet Quantity	1200

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 2202018](#)
- [Warranty - Industrial & Commercial Products](#)