

Support Grips, Single Eye, Single Weave, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.50-1.74"

By Hubbell Wiring Device-Kellems
Catalog # [02202019](#)

Support Grips, Single Eye, Single Weave, Split Mesh, Lace Closing, Tin-Coated Bronze, 1.50-1.74"



Application

- Single Eye

Performance

- Mechanical - Approximate Breaking Strength - 1,610 (7,161) Lbs. (N)
- Mechanical - Working Load - 161 (716.1) Lbs. (N)

General

Approx Breaking Strength	1,610 lbs
Catalog Number	02202019
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Equalizer - Bronze• Eye - Copper• Lace - Tin-coated bronze• Strand - Tin-coated bronze• Tag - Mylar

Style	Split Mesh, Lace Closing
Type	Single Eye
UPC	783585302249

Conductor Related

Cable Diameter Range	1.5 in-1.74 in
Cable Size	1.50"-1.74" (3.81-4.42)

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	10
Pallet Quantity	900

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 2202019](#)
- [Warranty - Industrial & Commercial Products](#)