

Support Grips, Single Eye, Single Weave, Split Mesh, Lace Closing, Tin-Coated Bronze, 2.00-2.49"

By Hubbell Wiring Device-Kellems
Catalog # [02202021](#)

Support Grips, Single Eye, Single Weave, Split Mesh, Lace Closing, Tin-Coated Bronze, 2.00-2.49"



Application

- Single Eye

Performance

- Mechanical - Approximate Breaking Strength - 3,260 (14,500) Lbs. (N)
- Mechanical - Working Load - 326 (1450) Lbs. (N)

General

Approx Breaking Strength	3,260 lbs
Catalog Number	02202021
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Equalizer - Bronze• Eye - Copper• Lace - Tin-coated bronze• Strand - Tin-coated bronze

Style
Type
UPC

- Tag - Mylar
- Split Mesh, Lace Closing
Single Eye
783585302287

Conductor Related

Cable Diameter Range 2 in-2.49 in
Cable Size 2.00"-2.49" (5.08-6.32)

Certifications And Compliance

Industry Standard(s) CSA Certified

Logistics

Carton Quantity 50

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 2202021](#)
[Warranty - Industrial & Commercial Products](#)