

## Support Grips, Single Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.75-0.99"

By Hubbell Wiring Device-Kellems  
Catalog # [02203015](#)



Support Grips, Single Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 0.75-0.99"

### Application

- Single Eye

### Performance

- Mechanical - Approximate Breaking Strength - 1,020 (4,537)
- Mechanical - Working Load - 102 (453.7) Lbs. (N)

### General

Approx Breaking Strength	1,020 lbs
Catalog Number	02203015
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none"><li>• Equalizer - Bronze</li><li>• Eye - Copper</li><li>• Rod - Stainless Steel</li><li>• Strand - Tin-coated bronze</li><li>• Tag - Mylar</li></ul>
Style	Split Mesh, Rod Closing

Type	Single Eye
UPC	783585303055

### Conductor Related

Cable Diameter Range	0.75 in-0.99 in
Cable Size	.75"- .99" (1.90-2.51)

### Certifications And Compliance

Industry Standard(s)	CSA Certified
Standards - RoHS Compliance Status	CM

### Logistics

Carton Quantity	10
Pallet Quantity	2400

### Product Assets

[Catalogs - WDK Catalog Full 2024](#)  
[Literature - Wire Management Solutions Brochure](#)  
[Specifications - 2203015](#)  
[Warranty - Industrial & Commercial Products](#)