

Support Grips, Offset Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 2.50-2.99"

By Hubbell Wiring Device-Kellems
Catalog # [02203046](#)

Support Grips, Offset Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 2.50-2.99"



Application

- Offset Eye

Performance

- Mechanical - Approximate Breaking Strength - 3,100 (13,789)
- Mechanical - Working Load - 310 (1378.9) Lbs. (N)

General

Approx Breaking Strength	3,100 lbs
Catalog Number	02203046
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Eye - Copper• Rod - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar

Style	Split Mesh, Rod Closing
Type	Offset Eye
UPC	783585303284

Conductor Related

Cable Diameter Range	2.5 in-2.99 in
Cable Size	2.50"-2.99" (6.35-7.59)

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 2203046](#)
- [Warranty - Industrial & Commercial Products](#)