

Support Grips, Offset Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 3.50-3.99"

By Hubbell Wiring Device-Kellems
Catalog # [02203048](#)

Support Grips, Offset Eye, Single Weave, Split Mesh, Rod Closing, Tin-Coated Bronze, 3.50-3.99"



Application

- Offset Eye

Performance

- Mechanical - Approximate Breaking Strength - 4,900 (21,795)
- Mechanical - Working Load - 490 (2179.5) Lbs. (N)

General

Approx Breaking Strength	4,900 lbs
Catalog Number	02203048
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Eye - Stainless Steel• Rod - Stainless Steel• Strand - Tin-coated bronze• Tag - Mylar

Style	Split Mesh, Rod Closing
Type	Offset Eye
UPC	783585303307

Conductor Related

Cable Diameter Range	3.5 in-3.99 in
Cable Size	3.50"-3.99" (8.89-10.13)

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	10
-----------------	----

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 2203048](#)
- [Warranty - Industrial & Commercial Products](#)