

Support Grips, Double Eye, Double Weave, Closed Mesh, Tin-Coated Bronze, 1.00-1.24"

By Hubbell Wiring Device-Kellems
Catalog # [02206002](#)

Support Grips, Double Eye, Double Weave, Closed Mesh, Tin-Coated Bronze, 1.00-1.24"



Application

- Double Eye

Performance

- Mechanical - Approximate Breaking Strength - 4,280 (19,037)
- Mechanical - Working Load - 428 (1903.7) Lbs. (N)

General

Approx Breaking Strength	4,280 lbs
Catalog Number	02206002
Construction	Woven
EU RoHS Indicator	Yes
Material	Bronze, Tin Coated
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Heavy Duty
Specifications	<ul style="list-style-type: none">• Eye - Stainless Steel• Strand - Tin-coated bronze

Style
Type
UPC

- Tag - Mylar
- Closed Mesh, Double Weave
Double Eye
783585304366

Conductor Related

Cable Diameter Range	1 in-1.24 in
Cable Size	1.00"-1.24" (2.54-3.15)

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Specifications - 2206002](#)
- [Warranty - Industrial & Commercial Products](#)