

Support Grips, Offset Eye, Single Weave, Closed Mesh, Stainless Steel, 0.75-0.99"

By Hubbell Wiring Device-Kellems
Catalog # [02401039](#)

Support Grips, Offset Eye, Single Weave, Closed Mesh, Stainless Steel, 0.75-0.99"



Application

- Offset Eye

Performance

- Mechanical - Approximate Breaking Strength - 2,060 (9,163)
- Mechanical - Working Load - 206 (916.3) Lbs. (N)

General

Approx Breaking Strength	2,060 lbs
Catalog Number	02401039
Construction	Woven
EU RoHS Indicator	Yes
Material	Stainless Steel
Material - Mounting Hardware	Screw Hook or Beam Clamp
Series	Standard Duty
Specifications	<ul style="list-style-type: none">• Eye - Stainless Steel• Strand - Stainless Steel• Tag - Mylar
Style	Closed Mesh, Single Weave

Type
UPC

Offset Eye
783585309347

Conductor Related

Cable Diameter Range
Cable Size

0.75 in-0.99 in
.75"--.99" (1.90-2.51)

Certifications And Compliance

Industry Standard(s)
CSA Certified

Logistics

Carton Quantity
Pallet Quantity

10
1200

Product Assets

[Catalogs - WDK Catalog Full 2024](#)
[Literature - Wire Management Solutions Brochure](#)
[Specifications - 2401039](#)
[Warranty - Industrial & Commercial Products](#)