

# Kellems Wire Pulling Grips, Underground Rotating Eye, 1.00- 1.49 in, Standard

By Hubbell Wiring Device-Kellems

Catalog # [03301025](#)

Kellems Wire Management, Pulling Grips, Underground Rotating  
Eye, 1.00-1.49", Standard



## General

Application	Underground Pulling
Approx Breaking Strength	16,400 lbs
Catalog Number	03301025
Color	
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	3280
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Performance	Mechanical - Approximate Breaking Strength - 16,400 (72,947) Lbs. (N)  Mechanical - Cable Diameter Range - 1.00"-1.49" (2.54-3.78)  Mechanical - Working Load - 3280 (14589.4) Lbs. (N)
Series	Underground K-Type
Style	Closed Mesh, Double Weave
Type	Rotating Eye, Standard Length
UPC	783585314297
Working Load Limit	3,280 lb

## Dimensions

Weight	4.2 lb
--------	--------

## Conductor Related

Cable Diameter Range	1.00 in - 1.49 in
Cable Diameter Range Metric	2.54 cm - 3.78 cm
Cable Size	1.00"-1.49" (2.54-3.78)
Cable Specification	UL Listed Circuit Wire

## Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

## Logistics

Carton Quantity	5
Pallet Quantity	200

## Product Assets

[Catalogs - WDK Catalog Full 2024](#)

[Literature - Wire Management Solutions Brochure](#)

[Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved  
WDK\_MX-03301025-SPEC-EN | REV 6/2024