

Kellems Wire Pulling Grips, Underground Rotating Eye, 1.50- 1.99 in, Standard

By Hubbell Wiring Device-Kellems

Catalog # [03301026](#)

Kellems Wire Management, Pulling Grips, Underground Rotating Eye, 1.50-1.99", Standard



General

Application	Underground Pulling
Approx Breaking Strength	16,400 lbs
Catalog Number	03301026
Color	
Construction	Woven
EU RoHS Indicator	Yes
Load Capacity	3280
Material	Steel, Galvanized
Material - Mounting Hardware	Non-Mounted
Performance	Mechanical - Approximate Breaking Strength - 16,400 (72,947) Lbs. (N) Mechanical - Cable Diameter Range - 1.50"-1.99" (3.81-5.05) Mechanical - Working Load - 3280 (14589.4) Lbs. (N)
Series	Underground K-Type
Style	Closed Mesh, Double Weave
Type	Rotating Eye, Standard Length
UPC	783585314303
Working Load Limit	3,280 lb

Dimensions

Weight	2.3 lb
--------	--------

Conductor Related

Cable Diameter Range	1.50 in - 1.99 in
Cable Diameter Range Metric	3.81 cm - 5.05 cm
Cable Size	1.50"-1.99" (3.81-5.05)
Cable Specification	UL Listed Circuit Wire

Certifications And Compliance

Industry Standard(s)	CSA Certified
----------------------	---------------

Logistics

Carton Quantity	5
-----------------	---

Product Assets

- [Catalogs - WDK Catalog Full 2024](#)
- [Literature - Wire Management Solutions Brochure](#)
- [Warranty - Industrial & Commercial Products](#)



A Hubbell brand

©2024 Hubbell Incorporated. All rights reserved
WDK_MX-03301026-SPEC-EN | REV 6/2024